

Guardini®

MADE in ITALY

Rossana



LOW-CURE
190°C
MAX

INSTRUCTIONS FOR USE

1. Wash the mould before the first use.
2. Grease inside surface with oil, butter or margarine before baking.
3. Allow cake to cool down a little before removing from the mould.
4. Do not use on a flame or other direct heat source, including stove tops.
5. Use only in traditional ovens (no microwave).
6. Please do not use sharp objects or others metal tools which could damage the baking pan surface.
7. Please do not exceed 190° C.
8. For the cleaning of the mould (after each use), we recommend hand washing with dish soap and it is recommended to dry the mould immediately after washing.

Do not use the empty mould in the oven, because it may damage, compromising its quality.

TECHNICAL DATA

Body metal	Hi-Top steel
Non-stick coating	Xylan
External color	red
Internal color	grey

BENEFIT LINE



OPTIMIZED THICKNESS

Non-stick coating specially designed, with a low thickness, which guarantees excellent results for uniform cooking.


PLUS LINE



Temperature



Non-stick



Non-stick layers



Scratch resistance



Warranty



All Guardini steel moulds with non-stick coating are BPA and PFOA free.

USES AND PROHIBITIONS

